
Rittal – The System.

Faster – better – everywhere.



VX 8618.801

Section for cable entry, center

State: 11/20/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8618.801 - Section for cable entry, center

The profile is attached directly on to the gland plates. his ensures that when the mounting plate is installed in the forward mounting position, the cables can be routed directly onto a cable clamp rail without large bending radii. In conjunction with the cable clamp rail, this enables optimum adjustment between the cable entry and mounting plate.



Features

Model No.	VX 8618.801
Benefits	Easy mounting Full-surface support High level of sealing of cables inserted into the enclosure
Applications	For top-mounting on base plates
Material	Hard PVC Flame-resistant, self-extinguishing Temperature resistant to +60 °C Seal: PU foam Cross-section: 30 x 25 mm
Supply includes	Plug-in sections, incl. foam rubber clamp strip
Note	Two pieces are required for each cable entry point For enclosures with 1,000 mm widths, the floor unit can be divided into two sections. Two cable routing points (left/right) can be used

© Rittal 2026

Features

Suitable for	Enclosure type: VX: = 800 mm Enclosure type: VX SE Enclosure type: CX Pedestal Enclosure type: CX One-Piece Console Enclosure type: VX: = 31.5 ″ Enclosure type: VX SE Enclosure type: CX Pedestal Enclosure type: CX One-Piece Console
Packaging unit	2 pc(s).
Net weight	0.22 kg
Gross weight	0.24 kg
Customs tariff number	39269097
ETIM 9	EC000211
ECLASS 8.0	27142421
Product description	VX Section for cable entry, centre, for W: 800 mm

© Rittal 2026