

Rittal – The System.

Faster – better – everywhere.



VX 8619.400

Cable clamp rail

State: 4/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.400 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

| | |
|---|--|
| Model No. | VX 8619.400 |
| Product description | Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth. |
| Material | Steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options VX | In enclosure width 400 mm, in the base |
| Installation options AX | In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX |
| Installation options AX stainless steel | In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX |
| Installation options VX Base | In base/plinth width/depth 400 mm, in conjunction with retaining/ spacer piece |
| Suitable for | VX base system |
| Dimensions | Length: 354 mm Length: 13.9 " |
| Suitable for | Enclosure type: VX AX Width: = 400 mm Enclosure type: VX AX Width: = 15.7 " |
| Suitable for width | 400 mm 15.7 " |

Features

| | |
|-----------------------|--|
| Packaging unit | 2 pc(s). |
| Net weight | 2 kg |
| Gross weight | 2.34 kg |
| Customs tariff number | 83024900 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | VX Cable clamp rail, mounting angle, for W: 400 mm |