

# Rittal – The System.

Faster – better – everywhere.



## VX 8619.440 Cable clamp rail

State: 4/22/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.440 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

## Features

Model No.	VX 8619.440
Product description	Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options VX	In enclosure width 1200 mm, in the base
Installation options VX SE	In enclosure width 1200 mm, in the base
Installation options AX	In enclosure width 1200 mm, in conjunction with the AX interior installation rail and AX base configuration rail
Installation options VX Base	In base/plinth width/depth 1,200 mm, in conjunction with retaining/spacer piece
Installation options VX base/plinth, stainless steel	In base/plinth width 1,200 mm, in conjunction with a M8 nut
installation options AX Base	In base/plinth width 1,200 mm
Suitable for	AX base/plinth system VX base system VX base/plinth system, stainless steel
Dimensions	Length: 1,154 mm Length: 45.4 "

# Features

---

Suitable for	Enclosure type: VX VX SE AX CX Pedestal CX One-Piece Console Width: = 1,200 mm Enclosure type: VX VX SE AX CX Pedestal CX One-Piece Console Width: = 47.2 "
Suitable for width	1,200 mm 47.2 "
Packaging unit	2 pc(s).
Net weight	5.64 kg
Gross weight	6 kg
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	VX Cable clamp rail, mounting angle, for W: 1200 mm

---