

Rittal – The System.

Faster – better – everywhere.



WM 8017.585

WM wall-mounted disconnect enclosure

State: 5/21/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.585 - WM wall-mounted disconnect enclosure

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

| | |
|---------------------|--|
| Model No. | WM 8017.585 |
| Product description | These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel. |
| Material | Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Dipcoat-primed and powder-coated, textured paint |
| Color | RAL 7035 |
| Supply includes | Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Flange door with universal disconnect cutout 3-point latching L-Handle |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 825 mm Height: 1,050 mm Depth: 300 mm Width: 32.5 " Height: 41.3 " Depth: 11.8 " |
| Dimensions of mounting plate (W x H) | 730 mm x 1,020 mm 28.7 " x 40.2 " |
| Protection category NEMA | NEMA 4 UL Type 4/3R/12 |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 2 mm 0.08 " |
| Material thickness – mounting plate | 3 mm 0.12 " |
| Packaging unit | 1 pc(s). |
| Weight/packaging unit | 74 kg 163.1 lb. |
| Customs tariff number | 7326909099 |
| UPC-Code | 83162 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |