

Rittal – The System.

Faster – better – everywhere.



WM 8017.590

WM wall-mounted enclosure

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.590 - WM wall-mounted enclosure double door

These double door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.

Features

| | |
|--------------------------------------|----------------------------------------------------------------------------------------------------------|
| Model No. | WM 8017.590 |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel |
| Surface finish | Dipcoat-primed and powder-coated, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with door(s) Mounting plate Rear wall mounting holes |
| Dimensions | Width: 1,200 mm Height: 1,200 mm Depth: 300 mm Width: 47.2 " Height: 47.2 " Depth: 11.8 " |
| Dimensions of mounting plate (W x H) | 1,150 mm x 1,150 mm 45.3 " x 45.3 " |
| Protection category NEMA | NEMA 12 NEMA 12 |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 2 mm 0.08 " |
| Material thickness - mounting plate | 2.5 mm 0.1 " |

Features

| | |
|------------------------|------------|
| 3-point locking system | Yes |
| Number of doors | 2 |
| Packaging unit | 1 pc(s). |
| Net weight | 209.436 lb |
| Gross weight | 210 lb |
| Customs tariff number | 8538100000 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
