
Rittal – The System.

Faster – better – everywhere.




VX 8619.720

System chassis 14 x 39 mm


State: 11/20/2026 (Source: www.rittal.com/us-en)

VX 8619.720 - System chassis 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.







Features

Model No.	VX 8619.720
Product description	For securing cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between fixing points	475 mm
Suitable for door width	600 mm 23.6 ″
Installation options VX	In door width 600 mm
Installation options VX SE	In door width 600 mm
Installation options AX	In enclosure width 500 mm and in enclosure height 600 mm, in conjunction with rail for interior installation AX In housing width 1200 mm in lockable door
Installation options AX stainless steel	In enclosure height 600 mm

Features

Installation options AX plastic	In door width 600 mm
Installation options for 3-part AX	In enclosure depth 673 mm or in the width of the wall section
Installation options PC	In door width 600 mm
Installation options CX	In door width 600 mm
Mounting tip	For installation in AX carbon steel, only in conjunction with rails interior installation AX
Note	Carbon steel screws or M5 self-tapping screws are required for extension with own components on the system chassis
Suitable for	Enclosure type: VX VX SE PC AX AX wall-mounted housing, 3-part CX One-Piece Console CX Pedestal Suitable for width or height or depth: 600 mm
Packaging unit	4 pc(s).
Net weight	0.956 kg
Gross weight	1.14 kg
PCF/VE (cradle-to-gate)	7.78
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 14 x 39 mm, for door width: 600 mm

Approvals

Explanations	PCF-declaration