

Rittal – The System.

Faster – better – everywhere.



VX 8619.730

System chassis 14 x 39 mm

State: 6/12/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.730 - System chassis 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

Model No.	VX 8619.730
Product description	For securing cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between fixing points	675 mm
Suitable for door width	800 mm 31.5 "
Installation options VX	In door width 800 mm
Installation options VX SE	In door width 800 mm
Installation options AX	In enclosure height 800 mm, in conjunction with rail for interior installation AX
Installation options AX stainless steel	In enclosure height 800 mm
Installation options AX plastic	In door width 800 mm

Features

Installation options PC	In door width 800 mm
Installation options CX	In door width 800 mm
Installation options VX Base	In base/plinth width 850 mm for mounting on base/plinth corner pieces
Mounting tip	For installation in AX carbon steel, only in conjunction with rails interior installation AX
Note	Carbon steel screws or M5 self-tapping screws are required for extension with own components on the system chassis
Suitable for	Enclosure type: VX VX SE PC AX AX plastic CX One-Piece Console CX Pedestal Suitable for width or height or depth: 800 mm
Suitable for	VX base system
Packaging unit	4 pc(s).
Net weight	1.4 kg
Gross weight	1.588 kg
PCF/VE (cradle-to-gate)	10.52
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 14 x 39 mm, for door width: 800 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------