

Rittal – The System.

Faster – better – everywhere.



VX 8620.053

Base/plinth corner pieces with
base/plinth trim panels, front and
rear, 100 mm stainless steel

State: 8/22/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.053 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm stainless steel for VX, TS, VX SE

Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.

Features

| | |
|---------------------|--|
| Model No. | VX 8620.053 |
| Product description | Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers. |
| Material | Base/plinth corner piece: Stainless steel 1.4301 (AISI 304) Base/plinth trim panels, front/rear: Stainless steel 1.4301 (AISI 304) Corner and baying covers: Plastic |
| Surface finish | Trim Panel: Brushed, grain 400 |
| Supply includes | 4 x base/plinth corner pieces 4 x corner covers 1 x baying cover 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components |
| Note | Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system |
| Dimensions | Height: 100 mm Height: 3.94 " |

Features

| | |
|---------------------------------|---|
| Suitable for | Width: = 1,200 mm Width: = 47.2 " |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| Weight/packaging unit | 9.46 kg 20.9 lb. |
| Packaging unit | 2 pc(s). |
| Net weight | 6.38 |
| Gross weight | 6.58 |
| Customs tariff number | 94039910 |
| EAN | 4028177922327 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|