## Rittal - The System.

Faster – better – everywhere.





## VX 8620.090 Base/plinth trim panels, vented

State: 11/29/2025 (Source: rittal.com/us-en)



# VX 8620.090 - Base/plinth trim panels, vented For VX base/plinth systems

For enclosure ventilation through the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Due to the complete symmetry of the VX base/plinth system, the vented trim panels can be mounted either at the front, at the back or at the side of the base/plinth corner piece.

#### **Features**

Model No.	VX 8620.090
Product description	For enclosure ventilation through the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Due to the complete symmetry of the VX base/plinth system, the vented trim panels can be mounted either at the front, at the back or at the side of the base/plinth corner piece.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: VX TX CableNet Suitable for width/depth: 600 mm Enclosure type: VX TX CableNet Suitable for width/depth: 23.6 "

© Rittal 2025

2

## Features

T		
Type rating according to UL 50E	Type 1, 12	
Weight/packaging unit	1.3 kg	
	2.9 lb.	
Packaging unit	2 pc(s).	
Net weight	1	
Customs tariff number	94039910	
EAN	4028177922433	
E-Number Sweden	E3465079	
ETIM 9	EC000721	
ECLASS 8.0	27182003	

## **Approvals**

Approvals UL + C-UL - FTTA