

**Rittal – The System.**

Faster – better – everywhere.



**VX 8620.400**

**Base/plinth expansion angle**

State: 4/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8620.400 - Base/plinth expansion angle for base/plinth system VX, stainless steel

For upgrading the base/plinth with system chassis or cable clamp rail. Suitable for 100 and 200 mm high base/plinth trim panels made from stainless steel.

## Features

Model No.	VX 8620.400
Product description	For upgrading the base/plinth with system chassis or cable clamp rail. Suitable for 100 and 200 mm high base/plinth trim panels made from sheet steel or stainless steel.
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	2 x installation angle brackets 2 mounting brackets for cable clamp rail Assembly components
For base/plinth trim height	100 mm 200 mm 3.94 " 7.87 "
Note	For interior installation on standing base/plinth trim panels The expansion angle is not needed for base/plinth trim panels rotated through 90° as the system perforation in the base/plinth trim panels can be used directly in this position
Weight/packaging unit	0.232 kg 0.5 lb.
Packaging unit	2 pc(s).
Net weight	0.22 kg
Gross weight	0.232 kg
Customs tariff number	83024200
ETIM 9	EC000721
ECLASS 8.0	27189234

# Features

---

Product description

VX base/plinth installation bracket, for base/plinth stainless steel,  
for base/plinth trim panel H: 100 / 200 mm