


# Rittal – The System.

Faster – better – everywhere.



## JB 8018.122

### JB Junction box

State: 1/29/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# JB 8018.122 - JB Junction box Carbon steel

The JB enclosure offers protection for dense wiring and sensitive small instruments. These hinged cover junction boxes combine the advantages of the AE and KL series at an economical cost. Features include 180 degree hinge and slotted insert quarter turn latch. Foamed-in-place gasket and a knife-edge perimeter add extra protection.



## Features

Model No.	JB 8018.122
Material	Housing and door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	180° hinge Housing with door Mounting panel
Material thickness - door	1.5 mm 0.06 "
Material thickness - enclosure	1.5 mm 0.06 "
Material thickness – mounting plate	1.5 mm 0.06 "
Position door catch	left

# Features

---

Dimensions	Width: 150 mm Height: 300 mm Depth: 100 mm
	Width: 5.91 " Height: 11.8 " Depth: 3.94 "
Protection category IP to IEC 60 529	IP 66
Protection category NEMA	NEMA 4
Packaging unit	1 pc(s).
Net weight	5.511
Gross weight	6.678
Customs tariff number	8538100000
UPC-Code	83259

# Approvals

---

Approvals	UL
Explanations	Declaration of conformity