

# Rittal – The System.

Faster – better – everywhere.



## VX 8660.002

Base/plinth corner pieces with  
base/plinth trim panels, front and  
rear

State: 2/17/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8660.002 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.



## Features

Model No.	VX 8660.002
Benefits	<p>Reliable - very high stability of the base</p> <p>Flexible – numerous interior expansion options with the VX accessories</p> <p>Simple – flush finish between the baying points</p>
Material	<p>Base/plinth corner piece: Carbon steel</p> <p>Base/plinth trim panels, front/rear: Carbon steel</p> <p>Corner and baying covers: Plastic</p>
Color	RAL 9005
Supply includes	<p>4 x corner covers</p> <p>Assembly components</p> <p>4 x base/plinth corner pieces, 100 mm high</p> <p>2 x base/plinth trim panels, front/rear, 100 mm high</p>
Note	Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths

# Features

Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 600 mm Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 23.6 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	4.47 kg 9.9 lb.
Packaging unit	2 pc(s).
Net weight	4.22 kg
Gross weight	4.466 kg
PCF/VE (cradle-to-gate)	17 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC000721

# Features

---

ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base corner piece with base trim panel, front and rear, : 100 mm, for W H: 600 mm, carbon steel

# Approvals

---

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration