
Rittal - The System.

Faster – better – everywhere.





VX 8660.005

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 11/4/2025 (Source: rittal.com/us-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

INFRASTRUCTURE

SOFTWARE & SERVICE

VX 8660.005 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.







Features

VX 8660.005
Reliable - very high stability of the base
Flexible – numerous interior expansion options with the VX accessories
Simple – flush finish between the baying points
Base/plinth corner piece: Carbon steel
Base/plinth trim panels, front/rear: Carbon steel
Corner and baying covers: Plastic
RAL 9005
4 x corner covers
Assembly components
4 x base/plinth corner pieces, 100 mm high
2 x base/plinth trim panels, front/rear, 100 mm high
Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another or for interior installation of the bases/plinths

© Rittal 2025 2

Features

Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT
	TP PC IW CX
	Width: = 1,000 mm Enclosure type: VX VX IT VX SE
	TX CableNet TS TS IT
	TP PC IW CX Width: = 39.4 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	6.19 kg 13.6 lb.
Packaging unit	2 pc(s).
Net weight	6.18
Gross weight	6.188
PCF/VE (cradle-to-gate)	23.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978089

© Rittal 2025 3

Features

ETIM 9	EC000721	
ETIM 8	EC000721	
ECLASS 8.0	27182003	

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration

© Rittal 2025