Rittal - The System.

Faster – better – everywhere.





VX 8660.042 Base/Plinth Trim Panels, Side

State: 11/5/2025 (Source: rittal.com/us-en)



VX 8660.042 - Base/Plinth Trim Panels, Side for base/ plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.







Features

Model No.	VX 8660.042
Version	Closed
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 200 mm Height: 7.87 ″

© Rittal 2025 2

Features

Suitable for	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW CX
	Depth: = 500 mm
	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Depth: = 19.7 "
Type rating according to UL 50E	Type 1
	Type 12
Weight/packaging unit	2.52 kg
	5.6 lb.
Packaging unit	2 pc(s).
Suitable for	for base/plinth system VX, carbon steel
Net weight	2.38
Gross weight	2.524
PCF/VE (cradle-to-gate)	9.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978300

© Rittal 2025 3

Features

ETIM 9	EC000721	
ETIM 8	EC000721	
ECLASS 8.0	27182003	

Approvals

Explanations PCF-declaration

© Rittal 2025