

Rittal – The System.

Faster – better – everywhere.



VX 8660.042

Base/Plinth Trim Panels, Side

State: 2/10/2026 (Source: ittal.com/us-en)

VX 8660.042 - Base/Plinth Trim Panels, Side for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.



Features

Model No. VX 8660.042

Version Closed

Material Carbon steel

Color RAL 9005

Supply includes Assembly components

Dimensions
Height: 200 mm
Height: 7.87 "

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Depth: = 500 mm Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Depth: = 19.7 " |
| Type rating according to UL 50E | Type 1 Type 12 |
| Weight/packaging unit | 2.52 kg 5.6 lb. |
| Packaging unit | 2 pc(s). |
| Suitable for | for base/plinth system VX, carbon steel |
| Net weight | 2.38 |
| Gross weight | 2.524 |
| PCF/VE (cradle-to-gate) | 9.6 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177978300 |

Features

ETIM 9 EC000721

ETIM 8 EC000721

ECLASS 8.0 27182003

Approvals

Explanations PCF-declaration