



Rittal – The System.

Faster – better – everywhere.



VX 8660.045

Base/Plinth Trim Panels, Side

State: 2/10/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

VX 8660.045 - Base/Plinth Trim Panels, Side for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.



Features

Model No. VX 8660.045

Version Closed

Material Carbon steel

Color RAL 9005

Supply includes Assembly components

Dimensions Height: 200 mm
Height: 7.87 "

Features

Suitable for	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Depth: = 1,000 mm Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Depth: = 39.4 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	5.58 kg 12.3 lb.
Packaging unit	2 pc(s).
Suitable for	for base/plinth system VX, carbon steel
Net weight	5.54
Gross weight	5.912
PCF/VE (cradle-to-gate)	21.3 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978331

Features

ETIM 9 EC000721

ETIM 8 EC000721

ECLASS 8.0 27182003

Approvals

Explanations PCF-declaration