Rittal - The System.

Faster – better – everywhere.





VX 8660.090 Base/plinth trim panels, vented

State: 11/16/2025 (Source: rittal.com/us-en)



VX 8660.090 - Base/plinth trim panels, vented for base/plinth system VX, carbon steel

For enclosure ventilation through the base/plinth. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. With the optional panel attachment, the ventilated panels can also be mounted on the side of the base corner piece.

Features

Model No.	VX 8660.090
Version	Vented
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm
	Height: 3.94 "

© Rittal 2025 2

Features

Suitable for	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Suitable for width/depth: 600 mm
	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS TS IT
	TP
	PC
	IW
	CX
	Suitable for width/depth: 23.6 ″
Type rating according to UL 50E	Type 1
Type rating deceraing to ou our	Type 12
Majahata aka mina wait	
Weight/packaging unit	1.42 kg
	3.1 lb.
Packaging unit	2 pc(s).
Suitable for	for base/plinth system VX, carbon steel
Net weight	1
Gross weight	1.319
Customs tariff number	94039910
EAN	4028177982949
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

© Rittal 2025 3

Approvals

Explanations

PCF-declaration

© Rittal 2025 4