

Rittal – The System.

Faster – better – everywhere.



TS 8800.520 Cable duct

State: 4/12/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8800.520 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.



Features

| | |
|-----------------|---|
| Model No. | TS 8800.520 |
| Version | Width 50 mm, for assembly on a vertical enclosure section in the side panel area. |
| Benefits | <p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p> |
| Material | Hard PVC Flame-resistant, self-extinguishing |
| Color | Similar to RAL 7030 |
| Supply includes | Cable duct with cover |
| Bar width | 5.5 mm 0.22 " |
| Slot width | 4.5 mm 0.18 " |
| Note | Can be shortened for other enclosure sizes. |

Features

| | |
|-----------------------------|--|
| Dimensions | Width: 50 mm Height: 1,800 mm Depth: 80 mm Width: 1.97 " Height: 70.9 " Depth: 3.15 " |
| Suitable for | Enclosure type: TS VX SE PC IW Height: ≤ 2,000 mm Enclosure type: TS VX SE PC IW Height: ≤ 78.7 " |
| Operating temperature range | 60 °C 140 °F |
| Packaging unit | 8 pc(s). |
| Net weight | 9.944 kg |
| Gross weight | 10.52 kg |
| Customs tariff number | 39259020 |
| ETIM 9 | EC000012 |
| ECLASS 8.0 | 27400703 |
| Product description | TS Cable duct for vertical TS section, WHD: 50x1800x80 mm |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|