## Rittal – The System.

Faster – better – everywhere.





# WM 8018.708 WM wall-mounted enclosure

State: 12/1/2025 (Source: rittal.com/us-en)



# WM 8018.708 - WM wall-mounted enclosure stainless steel, with Roof Slope

The WMS slope top wallmount enclosure is designed for any environment that requires frequent washdowns. The 20 degree overhanging sloped roof prevents water from accumulating on top of the enclosure and door opening.

#### **Features**

Model No.	WM 8018.708
Material	Door: Stainless steel, all-round foamed-in PU seal
	Housing and door: Stainless steel 1.4301 (AISI 304)
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door
	Door hinged on left
	Mounting plate
	Wall mounting blind-nuts
	20° overhanging slope top
Dimensions	Width: 900 mm
	Height: 1,195 mm
	Depth: 400 mm
	Width: 35.4 "
	Height: 47 "
	Depth: 15.7 "
Dimensions of mounting plate (W	840 mm x 1,155 mm
x H)	33.1 ″ x 45.5 ″
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
	0.08 ″
Material thickness - enclosure	2 mm
	0.08 "
Material thickness – mounting	2.5 mm
plate	0.1 "

© Rittal 2025

### **Features**

Lock	Lock version: 3-point locking system
Packaging unit	1 pc(s).
Net weight	194.998
Gross weight	194.998
Customs tariff number	7326908688
UPC-Code	84055

# **Approvals**

Explanations Declaration of conformity

© Rittal 2025 3