
## Rittal – The System.

Faster – better – everywhere.





# TS 8800.755 Cable duct

State: 10/31/2025 (Source: rittal.com/us-en)



#### TS 8800.755 - Cable duct

With DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates. Predetermined breaking points on the webs and on the cable duct base.





#### **Features**

Model No.	TS 8800.755
Version	for mounting plates
	for mounting on VX system perforation
Product description	With DIN punchings for direct mounting on the enclosure section or
	on surfaces such as mounting plates. Predetermined breaking
	points on the webs and on the cable duct base.
Material	Hard PVC
	Flame-resistant, self-extinguishing
	Temperature resistant to +60 °C
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm
	0.22 ″
Slot width	4.5 mm
	0.18 ″

© Rittal 2025

### Features

Installation options	With DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates.  If the rear mounting plate is aligned flush with the enclosure frame (installation position ± 0 mm), then the horizontal cable ducts will be flush against the cable ducts mounted on the enclosure section 50 mm wide cable duct for separately positioned VX25 enclosures with side wall on the left and right vertical sections adjacent to the mounting plate
Note	Can be shortened for other dimensions.
Dimensions	Width: 50 mm  Depth: 80 mm  Length: 2,000 mm  Width: 1.97 "  Depth: 3.15 "  Length: 78.7 "
Packaging unit	18 pc(s).
Net weight	18.9
Customs tariff number	39259020
EAN	4028177919648
ETIM 9	EC000012
ECLASS 8.0	27400703

## Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3