
Rittal – The System.

Faster – better – everywhere.



TS 8802.065

Section for cable entry, rear

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8802.065 - Section for cable entry, rear for TS, TP

Inserted in base opening.

Features

Model No.	TS 8802.065
Product description	To seal the cable entry on the base opening.
Benefits	Particularly well-suited to cables with identical cross-sections When installing the mounting plate in the rearmost position, the cables may be routed directly without large bending radii.
Technical specifications	Foam rubber cable clamping profile: Cross-section: 30 x 25 mm
Applications	Mount directly on the base opening/base tray and base plate
Material	Extruded aluminum section Foam rubber cable clamping profile: PU foam
Supply includes	Plug-in sections, incl. foam rubber clamp strip
Note	2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1,000 mm, two base openings are provided. 4 units per enclosure may be fitted
Suitable for	Enclosure type: TS: = 600 mm Enclosure type: TP Enclosure type: TS: = 23.6 ″ Enclosure type: TP
Protection category IP to IEC 60 529	IP 55 if correctly installed
Packaging unit	2 pc(s).
Net weight	0.208 kg
Gross weight	0.21 kg
Customs tariff number	76042990
ETIM 9	EC002624
ECLASS 8.0	27189265

© Rittal 2026

Features

Product description	TS profile for cable entry, rear, for TS, VX SE, TP, for W: 600 mm

© Rittal 2026