

Rittal – The System.

Faster – better – everywhere.



VX 8100.740

Mounting chassis 23 x 64 mm

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8100.740 - Mounting chassis 23 x 64 mm for VX, VX SE

For variable and individual interior installation of the enclosure frame on the inner mounting level.



Features

| | |
|----------------------|---|
| Model No. | VX 8100.740 |
| Product description | For variable and individual interior installation of the enclosure frame on the inner mounting level. Mounting flush with enclosure frame. Due to additional mounting brackets, it can also be used with the pre-installed mounting plate and can also be cut to any required length. |
| Benefits | System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | 2 punched sections 4 mounting brackets Assembly components |
| Installation options | In VX on the inner mounting level on the enclosure section VX In VX SE on the vertical enclosure section in conjunction with adapter rail VX Between two chassis on inner mounting level |

Features

| | |
|-----------------------|--|
| Suitable for | Enclosure type: VX VX SE Width/depth: 400 mm Enclosure type: VX VX SE Width/depth: 15.7 " |
| Packaging unit | 2 pc(s). |
| Net weight | 1 kg |
| Gross weight | 1.006 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, without mounting flange 23 x 64mm, for WD: 400 mm |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|