


Rittal – The System.

Faster – better – everywhere.



VX 8106.245

Side wall, screwable, carbon steel

State: 2/2/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

VX 8106.245 - Side wall, screwable, carbon steel for VX

Side panels, screw-fastened, sheet steel, for VX.

Features

Model No.	VX 8106.245
Benefits	<p>Time-saving mounting through clip-on side panel holder</p> <p>Automatic potential equalization and higher EMC protection due to enclosure panel holders with internal grounding insert</p> <p>Easy positioning in height and depth with placement aid</p> <p>One-man installation</p> <p>Grounding stud with large, paint-free contact surface for optimal support</p>
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 7035
Supply includes	Assembly components
Suitable for	<p>Enclosure type: VX</p> <p>Height: = 2,000 mm</p> <p>Depth: = 600 mm</p> <p>Enclosure type: VX</p> <p>Height: = 78.7 "</p> <p>Depth: = 23.6 "</p>
Protection category IP to IEC 60 529	IP 55 IP 66
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Base material	Carbon steel
Packaging unit	2 pc(s).
Net weight	26
Gross weight	29

Features

PCF/VE (cradle-to-gate)	110.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177827417
E-Number Sweden	E3465116
ETIM 9	EC002524
ECLASS 8.0	27182101

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------