

**Rittal – The System.**

Faster – better – everywhere.



**TS 8802.100**

**Section for cable entry, center**

State: 6/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8802.100 - Section for cable entry, center for TS, TP

Inserted in base plate.



## Features

Model No.	TS 8802.100
Product description	To seal the cable entry between the base plates.
Benefits	Particularly well-suited to cables with identical cross-sections
Technical specifications	Foam rubber cable clamping profile: Cross-section: 30 x 25 mm
Applications	For top-mounting on base plates
Material	Extruded aluminum section Foam rubber cable clamping profile: PU foam
Supply includes	Plug-in sections, incl. foam rubber clamp strip
Note	2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1,000 mm, two base openings are provided. 4 units per enclosure may be fitted
Suitable for	Enclosure type: TS: = 1,000 mm Enclosure type: TP Enclosure type: TS: = 39.4 " Enclosure type: TP
Protection category IP to IEC 60529	IP 55 if correctly installed
Packaging unit	4 pc(s).
Net weight	0.32 kg

# Features

---

Gross weight	0.351 kg
Customs tariff number	76042990
ETIM 9	EC000211
ECLASS 8.0	27142421
Product description	TS profile for cable entry, centered, for TS, VX SE, TP, for W: 1000 mm

---