## Rittal - The System.

Faster – better – everywhere.





# VX 8840.100 Baying-enclosure system VX25

State: 11/16/2025 (Source: rittal.com/us-en)



# VX 8840.100 - Baying-enclosure system VX25 Base enclosure with glazed door

The VX base enclosure with glazed door for industrial applications: Enclosure frame with glazed door at the front, rear door, roof plate, split bottom plates. Perfectly suited for efficient enclosure assembly.







#### **Features**

Model No.	VX 8840.100		
Material	Enclosure frame: Carbon steel, 1.5 mm		
	Roof: Carbon steel, 1.5 mm		
	Viewing door: Single-pane safety glass, 3 mm		
	Rear door: Carbon steel, 2.0 mm		
	Base plates: Carbon steel, 1.5 mm		
Surface finish	Enclosure frame: Dipcoat-primed		
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the		
	outside, textured paint		
Color	RAL 7035		
Supply includes	Enclosure frame		
	Glazed aluminum door, front (180°)		
	Carbon steel door at the rear (130°)		
	Lock front and rear: 3 mm double-bit		
	Roof plate		
	Gland plate		

© Rittal 2025 2

## Features

Dimensions	Width: 800 mm		
	Height: 2,000 mm		
	Depth: 600 mm		
	Width: 31.5 "		
	Height: 78.7 "		
	Depth: 23.6 "		
Protection category IP to EN 60 529	IP 55		
Protection category NEMA	NEMA 1		
- ,	NEMA 12		
Type rating according to UL 50E	Type 1		
	Type 12		
IK code	IK08		
Base material	Carbon steel		
Packaging unit	1 pc(s).		
Net weight	82		
Gross weight	84.2		
PCF/VE (cradle-to-gate)	207.5 kg CO2 eq (Cat B)		
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared		
EAN	4028177951365		
ETIM 9	EC000261		
ECLASS 8.0	27180101		

# Approvals

Approvals	UL + C-UL (listed)	
Certificates	Surface finish Protection category	

© Rittal 2025 3

# **Approvals**

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025