### Rittal – The System.

Faster – better – everywhere.





# TS 8609.840 Divider panel

State: 11/1/2025 (Source: rittal.com/us-en)



## TS 8609.840 - Divider panel for TS

To shield individual enclosure cells. The symmetry of the frame system means the divider panel can also be used at the rear.



#### **Features**

Model No.	TS 8609.840
Product description	To shield individual enclosure cells. All-round, double edging for stability and to accommodate the seal. The symmetry of the enclosure frame means divider panels of the appropriate dimensions can also be fitted at the rear.
Applications	Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.
Material	Carbon steel, 1.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for	Enclosure type: TS 8  Height: = 1,800 mm  Depth: = 400 mm  Enclosure type: TS 8  Height: = 70.9 "  Depth: = 15.7 "
Installation options	Mounted on the outer mounting level  The inner level remains free for further expansion

© Rittal 2025

#### **Features**

Mounting tip	The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/concealed with a cover.
Protection category IP to IEC 60 529	IP 54
Packaging unit	1 pc(s).
Net weight	7.447
Gross weight	8
Customs tariff number	94039910
EAN	4028177208780
ETIM 9	EC002525
ECLASS 8.0	27182102

© Rittal 2025 3