## Rittal - The System.

Faster - better - everywhere.





# TS 8612.060 TS System Chassis 17 x 73 mm

State: 11/10/2025 (Source: rittal.com/us-en)



## TS 8612.060 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.







#### **Features**

Model No.	TS 8612.060
Version	For the inner mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	590 mm 23.2 ″
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

© Rittal 2025

### **Features**

Suitable for	Enclosure type: VX SE	
	TP PC IW Suitable for width/depth: 600 mm Enclosure type: VX SE TP PC	
		IW
		Suitable for width/depth: 23.6 "
Packaging unit	4 pc(s).	
Net weight	2.448	
Gross weight	2.64	
PCF/VE (cradle-to-gate)	10.1 kg CO2 eq (Cat B)	
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on	
class	the basis of the product weight and self-declared	
Customs tariff number	73269098	
EAN	4028177212091	
ETIM 9	EC002625	
ECLASS 8.0	27189234	

© Rittal 2025 3