

# Rittal – The System.

Faster – better – everywhere.



## DK 9055.312 Monitor/Keyboard Unit

State: 6/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 9055.312 - Monitor/Keyboard Unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



## Features

|   |   |
|---|---|
| Model No.                                       | DK 9055.312   |
| Product description                             | Maximum power consumption during operation without optional KVM switch: 32 W, maximum power consumption when closed, without optional KVM switch: < 1 W.                                      |
| Benefits  | Analog and digital video port<br>Cables are safely routed in the energy chain<br>Lockable at the front<br>Simple, one-man installation.   |
| Color   | RAL 7035  |
| Supply includes                                 | Monitor/Keyboard Unit, 1 U<br>VGA cable<br>DVI cable<br>USB Cable<br>Schuko power cable<br>with 17" TFT display and VGA/DVI connection<br>2 PS/2 cables<br>Keyboard<br>with integral touchpad |
| Rated operating voltage                         | 100 V - 240 V, 1~, 50 Hz/60 Hz  |
| Max. power consumption with closed monitor unit | 1 W   |

# Features

|                                     |   |
|-------------------------------------|---|
| Max. power consumption in operation | 32 W  |
| Interfaces                          | VGA (D-SUB HD 15-pole)<br>DVI<br>1 x USB<br>PS/2  |
| Connector (type)                    | Non-heating apparatus connector C14   |
| Layout                              | US English  |
| Dimensions                          | Width: 482.6 mm<br>Depth: 680 mm<br>Width: 19 "<br>Depth: 26.8 "  |
| Operating temperature range         | 5 °C...45 °C<br>41 °F...113 °F  |
| Installation dimensions             | Installation depth (min.): 680 mm<br>Installation depth (max.): 850 mm<br>Installation depth (min.): 26.8 "<br>Installation depth (max.): 33.5 "  |
| Display features                    | Diagonal: 432 mm (17")<br>Format: 4 : 3<br>Contrast ratio: Contrast ratio approx. 1000:1<br>Display brightness: 350 cd/m <sup>2</sup><br>Display resolution: 1280 x 1024 pixels<br>Number of colors: 16,700,000 |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 15.85 kg  |
| Gross weight                        | 17.25 kg  |
| Customs tariff number               | 85286200  |
| ETIM 9                              | EC001428  |
| ECLASS 8.0                          | 19200201  |
| Product description                 | DK Monitor/keyboard unit, WHD: 482.6 mm (19")x1 Ux680 mm, 100-240 V, 1~, 50/60 Hz, US-english, RAL 7035   |

# Approvals

---

Explanations

Declaration of conformity