

Rittal – The System.

Faster – better – everywhere.



TS 8612.140

TS System Chassis 17 x 73 mm

State: 5/30/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.140 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

| | |
|----------------------|--|
| Model No. | TS 8612.140 |
| Version | For the outer mounting level |
| Product description | For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure. |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly screws |
| Length | 340 mm 13.4 " |
| Installation options | On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure |
| Mounting tip | The rail for interior installation is required when installing in TP |

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX SE TP PC IW Width/depth: 400 mm Enclosure type: VX SE TP PC IW Width/depth: 15.7 " |
| Packaging unit | 4 pc(s). |
| Net weight | 1.4 kg |
| Gross weight | 1.46 kg |
| PCF/VE (cradle-to-gate) | 6.1 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS punched section with mounting flange, 17 x 73 mm, for outer mounting level: W/D: 400 mm, L: 340 mm |