


**Rittal – The System.**

Faster – better – everywhere.



# KEL 9303.000

## Ex Enclosures

State: 2/6/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



FRIEDHELM LOH GROUP

# KEL 9303.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel



## Features

Model No.	KEL 9303.000
Version	Ex Enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EU</p> <p>Ambient temperature range: -30 °C...+80 °C</p> <p>The specified temperatures can be limited by the installed equipment</p> <p>Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)</p>
Material	<p>Housing: Stainless steel 1.4301 (AISI 304)</p> <p>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal</p>
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Housing Cover

# Features

Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm Width: 7.87 " Height: 7.87 " Depth: 3.15 "
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66
Packaging unit	1 pc(s).
Net weight	1.9
Gross weight	2.04
Customs tariff number	94032080
EAN	4028177138582
ETIM 9	EC002503
ECLASS 8.0	27180502

# Approvals

Approvals	ATEX ATEX QA CQC-CCC IECEx IECEx QAR
Explanations	Attestation of Conformity