## Rittal – The System.

Faster – better – everywhere.





# KEL 9303.000 Ex Enclosures

State: 12/11/2025 (Source: rittal.com/us-en)



# KEL 9303.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel







#### **Features**

Model No.	KEL 9303.000
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU
	Ambient temperature range: -30 °C+80 °C
	The specified temperatures can be limited by the installed
	equipment
	Explosion protection category to EN 60 079: Equipment protection
	due to increased safety (Ex e), equipment protection due to
	enclosure (Ex tb)
Material	Housing: Stainless steel 1.4301 (AISI 304)
	Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in
	silicone seal
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 μm
Supply includes	Housing
	Cover

© Rittal 2025

### Features

Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm Width: 7.87 " Height: 7.87 "
	Depth: 3.15 "
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66
Packaging unit	1 pc(s).
Net weight	1.9
Gross weight	2.04
Customs tariff number	94032080
EAN	4028177138582
ETIM 9	EC002503
ECLASS 8.0	27180502

# **Approvals**

Approvals	ATEX
	ATEX QA
	CQC-CCC
	IECEx
	IECEx QAR
Explanations	Attestation of Conformity

© Rittal 2025 3