

# Rittal – The System.

Faster – better – everywhere.



## KEL 9303.000 Ex Enclosures

State: 4/16/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9303.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel



## Features

Model No.	KEL 9303.000
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Housing Cover

# Features

---

Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm Width: 7.87 " Height: 7.87 " Depth: 3.15 "
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60529	IP 66
Packaging unit	1 pc(s).
Net weight	1.9 kg
Gross weight	2.04 kg
Customs tariff number	94032080
ETIM 9	EC002503
ECLASS 8.0	27180502
Product description	KEL Ex enclosure, WHD: 200x200x80 mm, Stainless steel 1.4301, without mounting plate, Empty enclosure with screw-fastened cover

# Approvals

---

Approvals	ATEX ATEX QA CQC-CCC IECEX IECEX QAR
Explanations	Attestation of Conformity