

# Rittal – The System.

Faster – better – everywhere.



## TS 8612.150

## TS System Chassis 17 x 73 mm

State: 4/6/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.150 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



## Features

Model No.	TS 8612.150
Version	For the outer mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	440 mm 17.3 "
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

# Features

---

Suitable for	Enclosure type: VX SE TP PC IW Width/depth: 500 mm Enclosure type: VX SE TP PC IW Width/depth: 19.7 "
Packaging unit	4 pc(s).
Net weight	1.92 kg
Gross weight	1.96 kg
PCF/VE (cradle-to-gate)	7.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	TS punched section with mounting flange, 17 x 73 mm, for outer mounting level: W/D: 500 mm, L: 440 mm

---