Rittal – The System.

Faster – better – everywhere.





KEL 9306.000 Ex Enclosures

State: 11/18/2025 (Source: rittal.com/us-en)



KEL 9306.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel







Features

KEL 9306.000
Ex Enclosures
Zone 1 and 2 or 21 and 22 to 2014/34/EU
Ambient temperature range: -30 °C+80 °C
The specified temperatures can be limited by the installed
equipment
Explosion protection category to EN 60 079: Equipment protection
due to increased safety (Ex e), equipment protection due to
enclosure (Ex tb)
Housing: Stainless steel 1.4301 (AISI 304)
Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in
silicone seal
Housing: Brushed, grain 400, peak-to-valley height < 0.8 μm
Housing
Cover

© Rittal 2025

Features

Width: 300 mm Height: 300 mm
Depth: 120 mm Width: 11.8 ″
Height: 11.8 "
Depth: 4.72 "
Yes
Yes
Stainless steel 1.4301 (AISI 304)
IP 66
1 pc(s).
3.7
3.9
94032080
4028177138643
EC002503
27180502

Approvals

Approvals	ATEX	
	ATEX QA	
	CQC-CCC	
	IECEx	
	IECEx QAR	

© Rittal 2025 3