

Rittal – The System.

Faster – better – everywhere.



SV 9340.004 Busbar Supports

State: 4/16/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.004 - Busbar Supports For Flat Copper Busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.004
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Electrical UL ratings (SCCR)	22 kA - 600 V, support spacing 500 mm, busbars 15 x 5 - 25 x 10 mm 25 kA - 600 V, support spacing 500 mm, busbars 30 x 5/10 mm 30 kA - 600 V, support spacing 250 mm, busbars 15 x 5 - 25 x 10 mm 65 kA - 600 V, support spacing 250 mm, busbars 15 x 5 - 25 x 10 mm, fuse class L max. 800 A, JDDZ/7
Note on Model No.:	When 12 x 5/10 mm busbars are used, spacer 9340.090 must also be used The use of a base tray is required for UL applications. UL approval only applies in conjunction with AC application
Number of poles	4-pole
Suitable for Model No.	3580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005
With internal attachment	Yes
Center-to-center spacing of busbars	60 mm

Features

Suitable for busbars	12 x 5 - 30 x 10
Packaging unit	4 pc(s).
Net weight	0.84 kg
Gross weight	0.915 kg
Customs tariff number	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV Busbar support, 4-pole, 60 mm bar centre distance, for busbar WH: 12x5-30x10 mm, UL design

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK