


**Rittal – The System.**

Faster – better – everywhere.



**VX 8617.180**

**System chassis 23 x 64 mm**


State: 2/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



FRIEDHELM LOH GROUP

# VX 8617.180 - System chassis 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures.



## Features

|                              |   |
|------------------------------|---|
| Model No.                    | VX 8617.180   |
| Product description          | For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures.   |
| Benefits                     | Simply place in the system punchings and screw-fasten System punchings on all four sides<br>With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material                     | Carbon steel  |
| Surface finish               | Zinc-plated   |
| Supply includes              | Assembly components   |
| Installation options VX      | In enclosure height 1600 mm, on the inner mounting level  |
| Installation options VX SE   | In enclosure width 1600 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility  |
| Installation options VX Base | In base/plinth width 1,600 mm on the base/plinth panels, in conjunction with base/plinth installation bracket   |

# Features

|                       |   |
|-----------------------|---|
| Suitable for          | Enclosure type: VX<br>VX IT<br>VX SE<br>Suitable for width or height or depth: 1,600 mm |
| Suitable for          | VX base system  |
| Packaging unit        | 4 pc(s).  |
| Net weight            | 6.72  |
| Gross weight          | 6.92  |
| Customs tariff number | 73269098  |
| EAN                   | 4028177829183   |
| ETIM 9                | EC002620  |
| ECLASS 8.0            | 27189234  |