Rittal – The System.

Faster – better – everywhere.





VX 8617.501 Baying block, internal

State: 11/5/2025 (Source: rittal.com/us-en)



VX 8617.501 - Baying block, internal for VX, VX IT

Flexible positioning and mounting all around the baying station. Lateral mounting creates a flush and buildable surface on the profile.

Features

Model No.	VX 8617.501
Benefits	Mounting at the side provides for a flush surface suitable for top- mounting towards the profile and thus prevents collisions with installed equipment All-round mounting in the baying area possible
Material	Die-cast zinc
Supply includes	Baying block, internal Baying seal Assembly components
Note	For baying enclosures with a width/depth >800 mm, 2 PU are required for assembly
Suitable for	Enclosure type: VX VX IT
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Protection category IP to IEC 60 529	IP 55
Packaging unit	6 pc(s).
Net weight	0.822
Gross weight	0.86
Customs tariff number	76169990
EAN	4028177919334
E-Number Sweden	E3465118

© Rittal 2025

Features

ETIM 9	EC002622
ECLASS 8.0	27189263

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3