Rittal – The System.

Faster – better – everywhere.



SV 9340.050

Busbar Supports

State: 11/18/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9340.050 - Busbar Supports For Flat Copper Busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.050
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~ 1500 V (DC)
Note on Model No.:	The use of a base tray is required for UL applications.
Electrical UL ratings (SCCR)	14 kA - 600 V, support spacing 500 mm, busbars 12 x 5/10 mm 22 kA - 600 V, support spacing 500 mm, busbars 15 x 5 - 25 x 10 mm 25 kA - 600 V, support spacing 250 mm, busbars 12 x 5/10 mm 25 kA - 600 V, support spacing 500 mm, busbars 30 x 5/10 mm 30 kA - 600 V, support spacing 250 mm, busbars 15 x 5 - 25 x 10 mm 50 kA - 600 V, support spacing 350 mm, busbars 30 x 5/10 mm, Fuse Class L max. 800 A, JDDZ/7 54 kA - 600 V, support spacing 500 mm, busbars 30 x 5/10 mm, circuit breaker max. 600 A, DIVQ/7 65 kA - 480 V, support spacing 250 mm, busbars 30 x 5/10 mm, circuit breaker max. 600 A, DIVQ/7 73 kA - 600 V, support spacing 250 mm, busbars 30 x 5/10 mm, fuse class L max. 800 A, JDDZ/7
Number of poles	3-pole

© Rittal 2026

Features

Suitable for Model No.	3580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005
With internal attachment	Yes
Center-to-center spacing of busbars	60 mm
Suitable for busbars	12 x 5 - 30 x 10
Packaging unit	4 pc(s).
Net weight	0.668 kg
Gross weight	0.72 kg
Customs tariff number	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV busbar support, 3-pole, 60 mm, bar center distance, for busbars WxH: 12x5-30x10 mm, UL design

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK