

Rittal – The System.

Faster – better – everywhere.



VX 8619.400 Cable clamp rail

State: 10/11/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.400 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.400
Product description	Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options VX	In enclosure width 400 mm, in the base
Installation options AX	In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
Installation options AX stainless steel	In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
Installation options VX Base	In base/plinth width/depth 400 mm, in conjunction with retaining/spacer piece
Suitable for	VX base system
Dimensions	Length: 354 mm Length: 13.9 "
Suitable for	Enclosure type: VX AX Width: = 400 mm Enclosure type: VX AX Width: = 15.7 "
Suitable for width	400 mm 15.7 "

Features

Packaging unit	2 pc(s).
Net weight	2
Gross weight	2.34
Customs tariff number	83024900
EAN	4028177921924
ETIM 9	EC000322
ECLASS 8.0	27400604