

**Rittal – The System.**

Faster – better – everywhere.



# VX 8619.470 Bracket/Spacer

State: 4/28/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.470 - Bracket/Spacer for base/plinth system VX, carbon steel

For flexible mounting of C-profile or cable clamp rails. For installation in the VX base or on the cabinet frame profile.



## Features

Model No.	VX 8619.470
Material	Die-cast zinc
Supply includes	2 retaining or spacer pieces Assembly components
Suitable for	Enclosure type: VX TS VX SE
Weight/package unit	0.298 kg 0.7 lb.
Packaging unit	2 pc(s).
Installation options	On the horizontal and vertical VX enclosure section On a system chassis for the inner mounting level On the vertical TS, VX SE enclosure section via snap-on nuts 8800.806 or via adapter rail for VX compatibility On the horizontal TS enclosure section On the horizontal VX SE enclosure section, bottom On the horizontal VX SE enclosure section top, in depth On enclosures and rails with rectangular hole profile 12.5 x 11 mm On base/plinth corner piece with base/plinth trim, front and rear On base trim panels, lateral
For thread	M8

# Features

Suitable for	for base/plinth system VX, carbon steel
Mounting tip	In VX SE on enclosure section in conjunction with adapter rail VX M8 x 16 mm cylinder screws with washers are required to fasten a C-profile rail
Net weight	0.28 kg
Gross weight	0.289 kg
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX retaining/spacer piece