


**Rittal – The System.**

Faster – better – everywhere.



**VX 8620.090**

**Base/plinth trim panels, vented**

State: 1/15/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))



# VX 8620.090 - Base/plinth trim panels, vented For VX base/plinth systems

For enclosure ventilation through the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Due to the complete symmetry of the VX base/plinth system, the vented trim panels can be mounted either at the front, at the back or at the side of the base/plinth corner piece.

## Features

Model No.	VX 8620.090
Product description	For enclosure ventilation through the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Due to the complete symmetry of the VX base/plinth system, the vented trim panels can be mounted either at the front, at the back or at the side of the base/plinth corner piece.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: VX TX CableNet Width/depth: 600 mm Enclosure type: VX TX CableNet Width/depth: 23.6 "

## Features

---

Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	1.3 kg 2.9 lb.
Packaging unit	2 pc(s).
Net weight	1
Customs tariff number	94039910
EAN	4028177922433
E-Number Sweden	E3465079
ETIM 9	EC000721
ECLASS 8.0	27182003

---

## Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------

---