

Rittal – The System.

Faster – better – everywhere.



SV 9340.620 OM adapter

State: 4/30/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.620 - OM adapter with tension spring clamp



Features

Model No.	SV 9340.620
Version	with tension spring clamp
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	65 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Without support frame, 1 x TS 55E, 1 x TS 55D
Number of poles	3-pole
Note on Model No.:	According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported
Dimensions	Width: 55 mm Height: 208 mm Width: 2.17 " Height: 8.19 "
Connection of round conductors	2.5 - 16 mm ²
Support rails Qty/height	2 / 10 mm 0.39 "

Features

Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Packaging unit	1 pc(s).
Net weight	0.299 kg
Gross weight	0.348 kg
Copper weight (kg per piece)	0.059
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 65 A, 690 V, 3-pole, tension spring clamp 2,5-16 mm², WH: 55x208 mm, support rail TS 55E, TS 55D

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK