

Rittal – The System.

Faster – better – everywhere.



VX 8620.094

Base/Plinth Trim Panels with Brush Strip

State: 2/2/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

VX 8620.094 - Base/Plinth Trim Panels with Brush Strip

For VX base/plinth systems

The 100 mm high base/plinth trim panels can be used in the depth or the width for cable entry into the base/plinth. The trim panels can also be used in 200 mm high base/plinths and they can be combined with other 100 mm high trim panels.

Features

Model No.	VX 8620.094
Product description	For cable entry into the base/plinth. If the base/plinth height is 200 mm, one or two trim panels with brush strips can optionally be used. The VX base/plinth system's complete symmetry allows the trim panels with brush strips to be mounted either at the front, rear or side of the base/plinth corner piece.
Material	Base/plinth trims: Carbon steel Brush strip: Plastic, self-extinguishing
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: VX TX CableNet Width/depth: 1,000 mm Enclosure type: VX TX CableNet Width/depth: 39.4 "
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	2.28 kg 5 lb.
Packaging unit	2 pc(s).
Net weight	2.08
Gross weight	2.28

Features

Customs tariff number 94039910

EAN 4028177922471

E-Number Sweden E3465077

ETIM 9 EC000721

ECLASS 8.0 27182003

Approvals

Approvals UL + C-UL - FTTA