
Rittal - The System.

Faster – better – everywhere.





VX 8640.008

Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm

State: 10/30/2025 (Source: rittal.com/us-en)

ICLOSURES >>> POWE

CLIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

VX 8640.008 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with molded self-positioning to the enclosure, can be used with or without base/plinth trim panel, depending on the application. Large openings in the base/plinth corner piece for optimal access to the screwing point, can be covered using plastic bay and corner covers.

Features

| Model No. | VX 8640.008 |
|---------------------|--|
| Product description | Heavy-duty base/plinth corner pieces with molded self-positioning to the enclosure, can be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimal access to the screw-fastening point, can be concealed with a plastic corner and baying cover. |
| Material | Base/plinth corner piece: Carbon steel |
| | Base/plinth trim panels, front/rear: Carbon steel |
| | Corner and baying covers: Plastic |
| Color | RAL 9005 |
| Supply includes | 4 x base/plinth corner pieces, 100 mm high |
| | 4 x corner covers |
| | 1 x baying cover |
| | 2 x base/plinth trim panels, front/rear, 100 mm high |
| | Assembly components |
| Note | Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths |
| Dimensions | Height: 100 mm |
| | Height: 3.94 ″ |

© Rittal 2025 2

Features

| Suitable for | Enclosure type: VX |
|---------------------------------|--------------------|
| | VX IT |
| | VX SE |
| | TS IT |
| | TX CableNet |
| | Width: = 1,600 mm |
| | Enclosure type: VX |
| | VX IT |
| | VX SE |
| | TS IT |
| | TX CableNet |
| | Width: = 63 " |
| Type rating according to UL 50E | Type 1 |
| | Type 12 |
| Weight/packaging unit | 7.8 kg |
| | 17.2 lb. |
| Packaging unit | 2 pc(s). |
| Net weight | 8.2 |
| Gross weight | 8.26 |
| Customs tariff number | 94039910 |
| EAN | 4028177958814 |
| E-Number Sweden | E3465367 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| | |

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3