

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.750 OM adapter

State: 5/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.750 - OM adapter with Connection Cables



## Features

Model No.	SV 9340.750
Version	With connection cable
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Connection cables (AWG)	AWG 8
Rated current max.	40 A
Rated operating voltage	690 V, 3~
Electrical UL ratings (SCCR)	30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with center-to-center spacing	60 mm
Length of connection cable	130 mm 5.12 "
Support rail type	Dimensions, 1 x 15 x 35 mm
Note	The technical data may vary for UL applications.
Number of poles	3-pole

# Features

---

Dimensions	Width: 55 mm Height: 208 mm Width: 2.17 " Height: 8.19 "
Support rails Qty/height	1 / 15 mm 0.59 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Approvals	UL
Packaging unit	1 pc(s).
Net weight	0.34 kg
Gross weight	0.381 kg
Copper weight (kg per piece)	0.088
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 40 A, 690 V, 3-pole, connection cable AWG 8, WH: 55x208 mm, metal support rail

# Approvals

---

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK