

Rittal – The System.

Faster – better – everywhere.



VX 8640.044

Base/plinth trim panels, side, 200 mm

State: 4/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.044 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.

Features

| | |
|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | VX 8640.044 |
| Product description | For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths. |
| Material | Carbon steel |
| Color | RAL 9005 |
| Supply includes | Assembly components |
| Dimensions | Height: 200 mm Height: 7.87 " |
| Suitable for | Depth: = 800 mm Depth: = 31.5 " |
| Type rating according to UL 50E | Type 1 Type 12 |
| Weight/packaging unit | 4.14 kg 9.1 lb. |
| Packaging unit | 2 pc(s). |
| Net weight | 3.94 kg |
| Gross weight | 4.14 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |

Features

| | |
|---------------------|------------------------------------------------------------------------|
| Product description | VX Base/plinth trim panel, side, H: 200 mm, for D: 800 mm, sheet steel |
|---------------------|------------------------------------------------------------------------|

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|