

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.820 Twin Cord

State: 6/4/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.820 - Twin Cord for OM adapters with spring cage terminal 2.5 – 16 mm<sup>2</sup>

Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.



## Features

Model No.	SV 9340.820
Product description	Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 10 = 5.26 mm <sup>2</sup> ÷ 6 mm <sup>2</sup>
Note	AWG = American Wire Gage
Dimensions	Length: 140 mm, 250 mm Length: 5.51 ~, 9.84 ~
Packaging unit	6 pc(s).
Net weight	0.138 kg
Gross weight	0.16 kg
Copper weight (kg per piece)	0.013
Customs tariff number	85444290
ETIM 9	EC000839
ECLASS 8.0	27400613

# Features

---

Product description

SV Twin cord, AWG 10, L1: 140 mm, L2: 250 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK