


Rittal – The System.

Faster – better – everywhere.



SV 9340.820 Twin Cord

State: 5/22/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.820 - Twin Cord for OM adapters with spring cage terminal 2.5 – 16 mm²

Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.



Features

Model No.	SV 9340.820
Product description	Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 10 = 5.26 mm² ÷ 6 mm²
Length	140 mm 250 mm 5.51 ~ 9.84 ~
Note	AWG = American Wire Gage
Dimensions	Length: 140 mm, 250 mm Length: 5.51 ~, 9.84 ~
Packaging unit	6 pc(s).
Weight/packaging unit	0.15 kg 0.3 lb.
Copper weight (kg per piece)	0.013

Features

Customs tariff number	74198090
EAN	4028177583573
ETIM 7.0	EC000839
ECLASS 8.0	27400613

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---