

Rittal – The System.

Faster – better – everywhere.



SV 9340.830

Twin Cord

State: 1/12/2026 (Source: ittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.830 - Twin Cord for OM adapters with spring cage terminal 2.5 – 16 mm²

Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.



Features

Model No.	SV 9340.830
Product description	Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 8 = 8.37 mm ² 10 mm ²
Note	AWG = American Wire Gage
Dimensions	Length: 140 mm, 250 mm Length: 5.51 „, 9.84 „
Packaging unit	6 pc(s).
Net weight	0.18
Gross weight	0.248
Copper weight (kg per piece)	0.02
Customs tariff number	85444290
EAN	4028177673861
ETIM 9	EC000839

Features

ECLASS 8.0

27400613

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK