Rittal - The System.

Faster – better – everywhere.





VX 8660.021

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 11/7/2025 (Source: rittal.com/us-en)

CLOSURES >>> POWER DIS


LIMATE CONTROL

INFRASTRUCTURE

SOFTWARE & SERVICES

VX 8660.021 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.



Features

Model No.	VX 8660.021
Benefits	Reliable - very high stability of the base Flexible – numerous interior expansion options with the VX accessories Simple – flush finish between the baying points
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x corner covers Assembly components 4 x base/plinth corner pieces, 200 mm high 1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths

© Rittal 2025 2

Features

Dimensions	Height: 200 mm Height: 7.87 ″
Suitable for	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Width: = 400 mm
	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Width: = 15.7 "
Type rating according to UL 50E	Type 1
	Type 12
Weight/packaging unit	5.85 kg
and partiagning and	12.9 lb.
Packaging unit	2 pc(s).
Net weight	5.846
Gross weight	5.85
PCF/VE (cradle-to-gate)	22.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978126

© Rittal 2025 3

Features

ETIM 9	EC000721	
ETIM 8	EC000721	
ECLASS 8.0	27182003	

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration

© Rittal 2025